



V200

LED Curing Light





5W Blue Light LED


Time Settings: 3s, 5s, 10s, 15s, 20s, 25s, 30s, 35s, 40s

Maximum Light Intensity: 1600–1800 mW/cm²

Wavelength: 400nm~515nm

Three Operating Modes

Light Intensity Adjusting Function



P1: 1400-1600 mW/cm²

P2: 1050-1200 mW/cm²

P3: 700-800 mW/cm²

P: Power button

M: Mode selection

01 for Full Power Mode

02 for Progressing Mode

03 for Pulse Mode

04 for Light Intensity Adjusting Function

In Mode **04**, press the **T** button to choose

P1 **P2** **P3** then press M to confirm

T: Time setting—Selectable Time Presets

P

M

T




**All-Metal body with
enhanced tactile grip**



Constant light output

curing performance is unaffected by battery level



Available in four colors

Silver

Blue

Red

Green

